



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2031991-1
SDE JPT 12-24AWG ASSY



TE Part # 2031991-2
SDE JPT 12-24AWG DIE

Customers Also Bought



TE Part #160668-2
110 FASTIN FASTON,REC.,20-16 AWG, PTBR

TE Part #160691-5
FF 250 TAB 22-18AWG BR SILVER PLATED

TE Part #160860-2
FF 250 REC 0.5-1.0MM2 TPBR

TE Part #154719-1
250 HSG. PL MKI REC. NAT

TE Part #1-967622-1
TIMER, CONNECTOR HOUSING

TE Part #1-967627-1
AMP MCP, UNSEALED CONNECTOR HOUSING

TE Part #1393738-4
V42254A6000G137=SUB D GEHAEUSE

TE Part #967632-1
2. KONT-SICHERUNG 12P

TE Part #1-963745-2
SPECIAL TERMINAL 20-17 AWG SLIPB LP

TE Part #1-968873-3
AMP MCP 2.8, CONTACT (LP)

Documents

CAD Files

Customer View Model

[ENG_CVM_927776-6_A9.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_927776-6_A9.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_927776-6_A9.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English