

---

## Data sheet


---

### Article Description

#### Push-button Switch Type 3656

16 (2) A, 250 V, 2-pole, on/off-switch, T 125°C,  
with rubber seal,  
faston 6,3 mm,  
fitting dimensions  $\varnothing$  25 mm,  
for wall thickness 0.7 to 2.5 mm,  
**dust and water proof according to IP 65,**  
approval mark: ENEC, UL

### Article picture



<i>inter BÄR-No.</i>	<i>colour rubber seal</i>	<i>Version button</i>
3656-295.22	black/red	illuminated
3656-250.22	black/green	illuminated
3656-001.22	black/black	non illuminated / <b>but push-button</b>

**Technical modifications reserved!**  
**Works at 230 V-mains must only be carried out by a specialist!**