


PXMBNI12FIM08ASCPG9 Datasheet



Product Name // M12 Series A Code Brass Nickel Plated
PG9 Inline Body 8 Contact Pins

View Product Page



// Product Description:

- M12 Series Brass Nickel Plated Inline Body Connectors
 - Water and dustproof to IP67 when mated with compatible connector
 - Pin only
 - 3, 4, 5, 8, 12 Contact (3, 8, 12 Contact are A Code, 4 Contact are choice of A Code A or D Code, 5 Contact are choice of A Code or B Code)
- Solder Terminals
 - Choice of gland nut sizes, depending on part code
 - Choice of Sealing Caps available separately to maintain IP rating of unmated connectors
 - Mate with M12 Series Flex Body and Panel Mount Connectors

// General Information:

Product Display Title:	M12 Series Brass Nickel Plated Inline Body Connectors
Product Family:	Circular Automation Connectors
Product Series:	M12 Series
Approvals:	CSA, ENEC, UL, VDE
Body Material:	Brass - Nickel Plated
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	2A
Diameter Over Coupling Ring Mm:	20mm
Function:	Inline Cable Connector Body
Ip Rating:	IP67
M12 Series Mounting Nut:	PG9
Max Operating Temperature:	+80°C
Min Operating Temperature:	-25°C
Number Of Contacts:	8 Contacts
Pin Layout Code:	A Code
Rohs Compliant:	Yes
Thread Size:	M12 x 1
Voltage Max:	30V

// Product PDF Links



// Product 3D CAD Model Links

