


4mm connectors

Order code	Manufacturer code	Description
17-0392	2211 100 NR	BLACK 4MM RETRACT. STK LEAD
17-0393	2211 100RG	RED 4MM RETRACT. STK LEAD
17-0450	2211 100BL	BLUE 4MM RETRACT. STK LEAD
17-0455	2211 100VERT	GREEN 4MM RETRACT. STK LEAD
17-0460	2211 100JAUNE	YELLOW 4MM RETRACT. STK LEAD

4mm connectors	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

4mm Retractable Test Leads

Photograph



Specification

Cable Insulation Material	:	Silicone
Connector Insulation Material	:	Polyamide
Connector Contact Material	:	Brass and Bronze Ni
Cable Cross Sectional Surface Area	:	0.75 mm ²
Voltage Rating	:	500V
Maximum Current	:	12A
Overall Contact Resistance	:	20mΩ
Temperature Range	:	-60°C to +180°C

Technical Drawing

