

**4mm connectors**



<b>Order code</b>	<b>Manufacturer code</b>	<b>Description</b>
17-1350	3295 NR AU/CO	BLACK SHROUDED 4MM SOCKET
17-1355	3295 BLEU AU/CO	BLUE SHROUDED 4MM SOCKET
17-1360	3295 VERT AU/CO	GREEN SHROUDED 4MM SOCKET
17-1365	3295 RG AU/CO	RED SHROUDED 4MM SOCKET
17-1370	3295 BLANC AU/CO	WHITE SHROUDED 4MM SOCKET
17-1375	3295 JAUNE AU/CO	YELLOW SHROUDED 4MM SOCKET
17-2350	3295-NOIR-NI	BLACK NICKEL 4MM SHROUDED SKT
17-2352	3295-BLEU-NI	BLUE NICKEL 4MM SHROUDED SKT
17-2354	3295-VERT-NI	GREEN NICKEL 4MM SHROUDED SKT
17-2356	3295-ROUGE-NI	RED NICKEL 4MM SHROUDED SKT
17-2358	3295-BLANC-NI	WHITE NICKEL 4MM SHROUDED SKT
17-2360	3295-JAUNE-NI	YELLOW NICKEL 4MM SHROUDED SKT

4mm connectors	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

## 4mm Shrouded Sockets – Push-fit

### Electro PJP – Standardised IEC 1010 Version

A range of professional quality push fit shrouded 4mm sockets offered in a wide range of colour's. By employing a novel design the sockets can simply be pushed into the required panel hole and are firmly held in position, significantly reducing assembly time. Specifically designed for use with shrouded 4mm plugs, but will also accept standard 4mm plugs. Solder termination. Suitable for panel thickness of 1 to 6mm. Available with nickel plated or gold plated contacts.




#### Specifications

Connector insulation material	: Polyamide
Connector contact material	: Brass
Connector plating	: Nickel or Gold
Voltage	: 1,000 V
Test voltage	: 50/60 Hz 1mn > 7400V
Maximum current	: 25 A
Resistance	: < 5mΩ
Mounting hole – Plastic	: Ø 12.2mm <sup>+0.2</sup> / <sub>-0</sub> – thickness > 1mm
Mounting hole – Metal	: Ø 12.5mm ±0.05 – thickness > 2mm

#### Mounting Details

- 1 Drill Ø accurately
- 2 Countersink lightly on setting side
- 3 Insert the socket manually
- 4 Push in with a plastic guide preferably, put on press



PJP Ref No.	Description	Colour
3295 N	4mm Push-fit Shrouded Socket – Gold Plated	Black
3295 Bl	4mm Push-fit Shrouded Socket – Gold Plated	Blue
3295 V	4mm Push-fit Shrouded Socket – Gold Plated	Green
3295 R	4mm Push-fit Shrouded Socket – Gold Plated	Red
3295 Bc	4mm Push-fit Shrouded Socket – Gold Plated	White
3295 J	4mm Push-fit Shrouded Socket – Gold Plated	Yellow
3295 N	4mm Push-fit Shrouded Socket – Nickel Plated	Black
3295 Bl	4mm Push-fit Shrouded Socket – Nickel Plated	Blue
3295 V	4mm Push-fit Shrouded Socket – Nickel Plated	Green
3295 R	4mm Push-fit Shrouded Socket – Nickel Plated	Red
3295 Bc	4mm Push-fit Shrouded Socket – Nickel Plated	White
3295 J	4mm Push-fit Shrouded Socket – Nickel Plated	Yellow