

1U Adjustable Mounting Depth Vented Rack Mount Shelf - 175lbs / 80kg

StarTech ID: ADJSHELF



The ADJSHELF Adjustable Mounting Depth Rack Mount Shelf offers a simple way to effectively organize mission critical computer hardware in your server racks and cabinets.

Compatible with all 19in (wide) server racks/cabinets, the fixed rack shelf can be adjusted from 19in to 38in (mount depth) as necessary. A sturdy cold-rolled steel construction provides long term durability and enables a weight capacity of up to 175 lbs (80 kg).

Backed by a StarTech.com 2-year warranty.

Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for mission critical hardware.

Features

- Low cost adjustable shelf for most 19 inch wide cabinets and racks
- adjustable mounting depth of 19" -38"
- TAA compliant for GSA Schedule purchases
- Vented shelf plate to preserve airflow
- Weight capacity up to 175 lbs (80 kg)



Technical Specifications

Warranty Lifetime

1U U Height

Weight Capacity 176.8 lb [80 kg]

Note Depth adjustable from 19-38"

Color Black

External Height 1.6 in [40 mm] External Width 18.9 in [480 mm] Internal Depth 27.6 in [700 mm] Internal Height 1.6 in [40 mm] Internal Width 17.6 in [446 mm] Maximum Mounting Depth 38.3 in [974 mm] Minimum Mounting Depth 19.5 in [495 mm] Product Height 1.6 in [40 mm] **Product Length** 27.6 in [700 mm]

Product Weight 155.3 oz [4400 g] **Product Width** 17.5 in [445 mm]

Shipping (Package) Weight 11.9 lb [5.4 kg]

Included in Package 1 - shelf

2 - front mounting brackets Included in Package 2 - rear mounting brackets Included in Package

Included in Package 8 - M5 screws Included in Package 8 - M5 cage nuts

Included in Package 1 - instruction manual

Certifications, Reports and Compatibility



