




| 4   | 3P Housing         | PA66     |             | 1    |
|-----|--------------------|----------|-------------|------|
| 3   | Terminals          | Brass    | Silver Ptd. | 3    |
| 2   | Negative Contactor | Copper   | Nickel Ptd. | 1    |
| 1   | Shield Cover       | Zn Alloy | Nickel Ptd. | 1    |
| No. | Description        | Material | Treat       | Q'ty |

**Specifications**  
**rating :**  
**100V AC 4A MAX**  
**contact resistance :**  
**pins-30mΩ MAX; shell-50mΩ MAX**  
**Insulation resistance :**  
**MIN 100 MEGΩ @500V DC**  
**voltage withstand :**  
**250V AC R.M.S. for 1 minute**