

### DESTB-1003

3 Pole steatite ceramic high temperature blocks terminal 57a 750v



#### SPECIFICATION

<b>Number of Poles</b>	3
<b>Body Material</b>	Steatite
<b>Colour</b>	White
<b>Min Conductor Size (Sq mm)</b>	2.5
<b>Max Conductor Size (Sq mm)</b>	16
<b>Min Conductor Size AWG</b>	18
<b>Max Conductor Size AWG</b>	8
<b>Max Current (A)</b>	57
<b>Max Voltage (V)</b>	750
<b>Minimum Temp Rating °C</b>	-40
<b>Max Temp Rating °C</b>	300-350
<b>Pitch (mm)</b>	18.5
<b>Height (mm)</b>	23
<b>Width (mm)</b>	30
<b>Length (mm)</b>	52
<b>Comments</b>	M4 conductor clamping screws, maximum torque=1.2Nm