


DESTB-0253

3 Pole steatite ceramic high temperature blocks terminal 24a 450v



SPECIFICATION

Number of poles	3
Body material	Steatite
Colour	White
Min conductor size (Sq mm)	1.5
Max conductor size (Sq mm)	4
Min conductor size AWG	22
Max conductor size AWG	12
Max current (A)	24
Max voltage (V)	450
Minimum temp rating °C	-40
Max temp rating °C	200
Pitch (mm)	11
Height (mm)	15.6
Width (mm)	18
Length (mm)	32
Comments	M3 conductor clamping screws, maximum torque=0.5Nm

