




### HYPS-01712

12 Pole plug & socket pillar block polyamide 6a 250v



Female Part



Male Part

### SPECIFICATION

Number of Poles	12
Body Material	Natural polyamide
Colour	Natural
Base Type	Raised
Max Conductor Size (Sq mm)	2.5
Max Current (A)	6
Max Voltage (V)	250
Max Temp Rating °C	105
Pitch (mm)	10
Height (mm)	15.10
Width (mm)	18.6
Length (mm)	116.15

### DISTRIBUTORS

