

1. Specifications:

Contact resistance:	30mΩ max.
Insulation resistance:	1000MΩ min.
Current rating:	1.5A
Voltage rating:	30V DC
Dielectric withstanding voltage:	AC 500V for 1 minute

2. Materials:

Housing:	PBT + 30% glass fiber (UL 94 – 0)
Contact:	Copper alloy
Shell:	Copper alloy

