


## JDAE12PA/SW

Venting element thread length 10 Black - RAL 9005



### SPECIFICATION

Product Type	Standard
Body Material	Polyamide
Min Temperature °C	-40
Max Temperature °C	100
IP Rating	IP66/IP67/IP69K
Colour	Black - RAL 9005
External Connecting Thread Type	Metric
Thread Length (mm)	10
Membrane	Polyether sulphone PES
Typical Air Flow	90 - 130 ml/min/cm <sup>2</sup> , 0,01 bar
Water Entry Pressure	> 1 bar
Width Across Flat 1 (mm)	17
Height (mm)	17.8
Connecting Thread Size	M12x1.5
Test Standard	Washers - Steel zinc-plated, Locknut - Brass CuZn39Pb3, nickel-plated, O-Ring - Nitrile rubber

### DISTRIBUTORS

