

DEDS1013

IP66, IK10 Lockable Solid door steel enclosure 1250x600x300 with galvanised wall mounting brackets. Power coated galvanised Grey (RAL 7035) steel housing and galvanised back plate guaranteed for 3 years against corrosion.



SPECIFICATION

Product Type	Solid door enclosures
Door Style	Solid
Enclosure Material	Steel
Door Material	Steel
IP Rating	66
Colour	Grey (RAL 7035)
Min Temperature °C	-20
Max Temperature °C	55
Size (mm)	1250x600x300
Height (mm)	1250
Width (mm)	600
Depth (mm)	300
Gland Plate (mm)	445x146
Mounting Plate (mm)	1215x550
Number of Locks	2
Comments	Lockable, with galvanized steel back plate and wall mounting brackets supplied
Accessories Available	Kwik fix cable gland

DISTRIBUTORS

