

**TEMPO TA241911**



Sample photo

**Order symbol:** TA241911  
**Product nbr:** 5814002  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074060747  
**El. number:**  
Finland: 3435686  
Denmark: 8212035043  
Norway:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

| Dimensions:                   |  | Length                     | Width | Height | Rating:                                    |
|-------------------------------|--|----------------------------|-------|--------|--------------------------------------------|
| <b>mm:</b>                    |  | 240                        | 191   | 107    | Ingress Protection (EN 60529): IP 65       |
| <b>inch:</b>                  |  | 9.4                        | 7.5   | 4.2    | Impact Resistance (EN 62262): IK 07        |
| <b>Materials:</b>             |  |                            |       |        | Electrical insulation: Totally insulated   |
| <b>Material:</b>              |  | ABS                        |       |        | Halogen free (DIN/VDE 0472, Part 815): Yes |
| <b>Base colour:</b>           |  | RAL 7035                   |       |        | Flammability Rating (UL 746 C 5): UL 94 HB |
| <b>Cover colour:</b>          |  | RAL 7035                   |       |        | Glow Wire Test (IEC 695-2-1) °C: 650       |
| <b>Cover screws material:</b> |  | Polyamide                  |       |        | <b>Certificates:</b>                       |
| <b>Cover screws colour:</b>   |  | Grey                       |       |        | Fimko                                      |
| <b>Gasket material:</b>       |  | PUR                        |       |        | Gost R                                     |
| <b>Temperatures:</b>          |  |                            |       |        |                                            |
| <b>Short term:</b>            |  | -40 ... 80 °C              |       |        |                                            |
| <b>Continuous:</b>            |  | -40 ... 60 °C              |       |        |                                            |
| <b>Short term:</b>            |  | -40 ... 175 °F             |       |        |                                            |
| <b>Continuous:</b>            |  | -40 ... 140 °F             |       |        |                                            |
| <b>Accessories:</b>           |  |                            |       |        |                                            |
| MP 2419                       |  | Mounting plate             |       |        |                                            |
| EKV 12                        |  | DIN-35 Mounting rail       |       |        |                                            |
| DR 210                        |  | DIN-35 Mounting rail       |       |        |                                            |
| FP 10674                      |  | Wall fastening lug (2 pcs) |       |        |                                            |
| DPS 14553                     |  | Grey sealing plug set      |       |        |                                            |

