

# M8 Stud Size 30A Blue Ring Connector Pack of 100

Order code: **33-0922**

**Note:**

- 1. Maximum electric current: 

|     |    |    |
|-----|----|----|
| AWG | 16 | 14 |
| AMP | 18 | 30 |
- 2. Maximum electrical rating: 105°C 600 volts max.
- 3. Insulation material: Vinyl
- 4. Insulator colour: Blue
- 5. Terminal material: Copper
- 6. Wire range: 16-14 AWG (1.5-2.5mm<sup>2</sup>)
- 7. Terminal surface treatment: Tin plated
- 8. Terminal thickness: 0.80mm

