

### Ring



Part Number	Stud Size
ERR3	3mm
ERR3.7	3.7mm
ERR4	4mm
ERR5	5mm
ERR6	6mm
ERR8	8mm
ERR10	10mm
ERR12	12mm

### Ring



Part Number	Stud Size
EBR3	3mm
EBR3.7	3.7mm
EBR4	4mm
EBR5	5mm
EBR6	6mm
EBR8	8mm
EBR10	10mm
EBR12	12mm

### Ring



Part Number	Stud Size
EYR3	3mm
EYR4	4mm
EYR5	5mm
EYR6	6mm
EYR8	8mm
EYR10	10mm
EYR112	12mm

### Spade



Part Number	Stud Size
ERF3	3.2mm
ERF3N	3.5mm
ERF4N	4mm
ERF5	5mm
ERF6	6mm

### Spade



Part Number	Stud Size
EBF3	3.2mm
EBF3N	3.5mm
EBF4N	4mm
EBF5	5mm
EBF6	6mm

### Spade



Part Number	Stud Size
EYF3N	3.5mm
EYF4N	4mm
EYF5	5mm
EYF6	6mm

### Butt

Part Number

ERB



### Blade



Part Number	Diameter x Length mm
ERBL10	2.3 x 10.4
ERBL18	2.3 x 18.4

### Blade



Part Number	Diameter x Length mm
EBBL9	2.8 x 9
EBBL18	2.3 x 18.4

### Blade



Part Number	Diameter x Length mm
EYBL10	2.8 x 10

### Pin



Part Number	Diameter x Length mm
ERP12	1.9 x 12

### Pin



Part Number	Diameter x Length mm
EBP12	1.9 x 12

### Pin



Part Number	Diameter x Length mm
ERP14	2.9 x 14

Durable low cost copper or brass connectors.  
Manufacturer as single piece connectors  
Electro tinned to protect from corrosion

Insulated with flared entry, colour coded  
vinyl sleeves  
All disconnect terminals supplied with  
anti-vibration copper sleeve.