


Insulated crimp connectors

Order code	Manufacturer code	Description
33-1274	DVP1-12	(PK 100) 1.9X12 RED 12A PIN CONTACT
33-1276	DVP2-12	1.9X12 BLUE 16A PIN CONTACT
33-1278	DVP5-14	2.9X14 YELLOW 20A PIN CONTACT


Insulated crimp connectors	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

Connectors - Single Pole

Pin Connector



Manufacturer Code	Description	P mm	d mm	L mm	Conductor Size mm ²	AWG	Single Strand
DVP1-12	Red 12A Pin Contact	12.0	1.9	21.2	0.25 to 1.65	22 to 16	0.57 to 1.44
DVP2-12	Blue 16A Pin Contact	12.0	1.9	21.2	1.04 to 2.63	16 to 14	1.14 to 1.82
DVP5-14	Yellow 20A Pin Contact	14.0	2.9	27.2	2.63 to 6.64	12 to 10	1.82 to 2.89



Davico Terminals are designed for easy application as indicated.

Suitable crimping tools:
DHC 15, DHC 15Y, DHCR 5,
DHCR 15, DBMT 1, 3 & 4.

