

Order code	Manufacturer code	Description
35-0041	n/a	12V LOW PROFILE BUZZER RC

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

SPECIFICATION

1. Rated Voltage 12VDC
2. Operating Voltage 3~15VDC
3. Max. Rated Current 30mA/5VDC
4. Min. Sound Pressure Level 85dB/10cm
5. Resonant Frequency 3100 ± 500 Hz
6. Response Time 50ms
6. Case Material PBT
7. Operating Temperature $-20 \sim +85^{\circ}\text{C}$
8. Store Temperature $-20 \sim +88^{\circ}\text{C}$
9. Weight 2g

