


| Order code | Manufacturer code | Description |
|------------|-------------------|------------------------------------|
| 35-0045 | n/a | MINIATURE PIEZO TRANSDUCER 15MM RC |

| | |
|--|--------------------------|
| | Page 1 of 2 |
| The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E. | Revision A 20/02/2007 |



SPECIFICATION

1. Rated Voltage12Vp-p Square Wave
2. Max. Allowable Voltage25Vp-p Square Wave
3. Max. Rated Current2mA at 4.0KHz/12Vp-p Square Wave
4. Resonant Frequency4.0±0.5KHz
5. Min. Sound Pressure Level.....75dB at 4.0KHz/12Vp-p Square Wave/10cm
6. Capacitance at 120Hz15000pF±30%
7. Case MaterialABS
8. Operating Temperature-20 ~ +60°C
9. Store Temperature-30 ~ +70°C
10. Weight1.3g

