

Order code	Manufacturer code	Description
35-0260	n/a	12V PCB PIEZO INDICATOR 3-16VDC (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

ABI-001-RC SPECIFICATION SHEET

Features:

- Colour: Black
- Housing Material: Noryl
- Built in oscillating circuit
- Wave solderable and washable
- Low power consumption

All data at 25°C unless otherwise specified.

SPECIFICATIONS	ABI-001-RC Piezo Indicator
Rated Voltage	12VDC
Operating Voltage	3~16VDC
Rated Current at rated voltage	7mA
Sound Output at 10cm, at rated voltage	≥80dB
Resonant Frequency at rated voltage	4000 ± 500Hz
Operating Temperature	-20 ~ +70°C
Storage Temperature	-30 ~ +80°C
Weight	1g

DIMENSIONS: (UNIT: mm, TOLERANCE: ±0.5mm)

