

Order code	Manufacturer code	Description
35-0286	n/a	9V PCB PIEZO TRANSDUCER (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

ABT-430-RC SPECIFICATION SHEET

Features:

- Colour: Black
- Housing Material: Noryl

All data at 25°C unless otherwise specified.

SPECIFICATIONS	ABT-430-RC Piezo Transducer
Rated Voltage (Vp-p Square Wave)	9Vp-p
Operating Voltage	1~30Vp-p
Rated Current at rated voltage	3mA
Capacitance at 120Hz	17000±30%pF
Sound Output at 4,000Hz at 10cm, at rated voltage	≥85dB
Resonant Frequency at rated voltage	4000 ± 500Hz
Operating Temperature	-20 ~ +60°C
Storage Temperature	-30 ~ +70°C
Weight	3g

DIMENSIONS: (UNIT: mm, TOLERANCE: ±0.5mm)

