


# Cat6 F/UTP 26awg LSOH Jacket Flush Moulded Snagless Patch Lead



# **FEATURES**

- ✓ Category 6
- ✓ Individually Bagged
- ✓ Flush Mould Strain Relief Boot
- ✓ Verified to ISO11801 ED.2 and ANSI/TIA/EIA

## **DESCRIPTION**

Velocity Category 6 F/UTP cables are manufactured, tested to the ISO11801 and EIA/TIA standards for enhanced performance. They are constructed with Shielded RJ45 plugs (50 micron gold) and quality Stranded Cat6 LSOH cable. These are available in 6 different lengths and manufactured in 5 colours.

#### **APPLICATIONS**

- ✓ 10 Base-T
- ✓ 100 Base-TX
- √ 1000 Base T Gigabit Ethernet
- ✓ 155 / 622 Mbps ATM

#### **SPECIFICATION**

- ✓ Conductor Cu Bare Copper 7/0.19
- ✓ Jacket LSOH Jacket
- ✓ Shield Al-Mylar Foil Screen Tinned Copper

## **COLOURS AVAILABLE**

Grey	RAL 7044
Red	RAL 3031
Blue	RAL 5012
Green	RAL 6016
Yellow	RAL 1023

