



Art No. FAN101

Case Fan 80x80x25mm, Black

Specification:

- Bearing System: Sleeve
- Operation Voltage (V DC): 6.0 ~ 13.8
- Rated Voltage (V DC): 12.00
- Rated Current (AMP): 0.16
- Input Power (Watt): 1.2
- Fan Speed (RPM): 2.500 +/-10%
- Air Volume (CFM): 42.50
- Noise Level (dBA): 32.60
- MTBF (hours/25C): 30.000
- Dimension (mm): 80x80x25
- Total Weight (gram): 75
- Connector Type: 4-pin

Package Content:

- 1 x Case Fan

Packaging Information:

- Packing Dimension: 80x80x25 mm
- Packing Weight: 0.065kg
- Carton Dimension: 440x270x370 mm
- Carton Q'ty: 200pcs
- Carton Weight: 13kgs

