



Art No. FAN103

Case Fan 120x120, Black

Specification:

- DC BRUSHLESS FAN
- BEARING TYPE: Sleeve
- RATING VOLTAGE: DC 12V
- RATING CURRENT: 0.23A \pm 10%
- RATED POWER: 2.78 \pm 10%W
- OPERATION TEMPERATURE: BELOW 70 degrees
- OPERATION VOLTAGE: DC 9V-13V
- START VOLTAGE: DC \leq 7V
- ROTATE SPEED: 2000 \pm 10% RPM
- MOST AIR FLOW: 40-45 CFM
- PERIOD OF USE: 30000-50000/H
- NOISE: 31.3 Db/a
- LEAD WIRE: 1007#26# 4pin wire, 280mm in length
- WEIGHT: 160G
- Dimension (mm): 120x120x25

Package Content:

- 1 x Case Fan

Packaging Information:

- Packing Dimension: 120x120x25 mm
- Packing Weight: 0.11kg
- Carton Dimension: 420x270x405 mm
- Carton Q'ty: 100pcs
- Carton Weight: 12kgs

* The specifications and pictures are subject to change without notice.
*All trade names referenced are the registered trademark of their respective owners.



RoHS
compliant



Made in China