



Art No. UA0072A

## USB2.0 Webcam, 8M Pixels

### Specification:

#### General

- Compliant to USB2.0/1.1 standard
- CMOS picture sensor: 0,3M pixels interpolated to 8M pixels
- Lens: F14mm, 54° angle, manual focus
- Color depth: 24-bit true color
- Image focus: 30mm to infinity; format: MPEG
- Built-in compression ratio (JPG)
- Automatic tracking, color equalizing, exposure and brightness balance adjustments
- Maximum resolution up to 1600 x 1200 (software enhanced)
- Supports video rates up to 30 fps (640 x 480, VGA), 6 fps (1600 x 1200, UVGA)
- Power consumption: 60mA

#### Physical

- 6 LED indicator and decorative lighting
- USB Cable: 1.5m
- Dimensions: 36mm x 58 mm x 75 mm
- Weight: 64g

### System Requirements:

- Windows 2000/XP/Vista/7 compatible
- PC with USB interface
- Pentium II 200/MMX/AMD K6 or above
- CD-ROM
- 200MB free disk space
- 32MB RAM or above

### Package Content:

- 1 x USB2.0 Webcam
- 1 x Software CD
- 1 x User Manual

### Packaging Information:

- Packing Dimension: 157x213x97 mm
- Packing Weight: 0.16kg
- Carton Dimension: 400x390x455 mm
- Carton Q'ty: 30pcs
- Carton Weight: 5kg



\* The specifications and pictures are subject to change without notice.  
\*All trade names referenced are the registered network of their respective owners.



Made in China