


Typ/Type

# UI39/21

Sicherheitstransformator  
 VDE 0570 / EN 61558 / ENEC10  
 UL 506 / CSA geprüft  
 Vakuumverguss  
 Temperaturklasse ta70°C/B  
 Cul-Gewicht: 170 g  
 Gesamt-Gewicht: 535 g



Nennleistung/Nominal power

# 30.0 VA

Safety transformer  
 VDE 0570 / EN 61558 / ENEC10  
 UL 506 / CSA approved  
 Vacuum casting  
 Temperature class ta70°C/B  
 Cul weight: 170 g  
 Total weight: 535 g



Bestell Nr. <i>Order No.</i>	Primär [V] <i>Primary</i>	Sekundär [V] <i>Secondary</i>	Strom [mA] <i>Current</i>	Stiftbelegung <i>Pin configuration</i>	Leerlaufspannung [V] <i>No load voltage</i>	Prüfzeichen / Approvals		
						VDE	UL 1585	UL 506
FLG39.21/60052-1	2x115	2x6	2x2500	1-4+7-10 / 11-13+18-20	2x6,70	●		●
FLG39.21/60053-1	2x115	2x7,5	2x2000	1-4+7-10 / 11-13+18-20	2x8,60	●		●
FLG39.21/60028-1	2x115	2x9	2x1666	1-4+7-10 / 11-13+18-20	2x10,60	●		●
FLG39.21/60029-1	2x115	2x12	2x1250	1-4+7-10 / 11-13+18-20	2x13,90	●		●
FLG39.21/60030-1	2x115	2x15	2x1000	1-4+7-10 / 11-13+18-20	2x17,30	●		●
FLG39.21/60054-1	2x115	2x18	2x833	1-4+7-10 / 11-13+18-20	2x20,90	●		●
FLG39.21/60055-1	2x115	2x24	2x625	1-4+7-10 / 11-13+18-20	2x27,30			●

Trenntransformator / isolation transformer