



## Specification Sheet

Catalogue No: **STTC26LA**

Description **Mini Oven**



Power:	220-240V 50HZ 2800W	Colour:	White with Stainless door handle
Control:	Manual	Plug Type:	BS Plug
Capacity:	26 Litre	Power Indicator Light:	Yes
Thermostat:	100 - 230°C	Power Cable:	0.9m
Timer:	60 min timer with bell ring	Approval:	CE / A13
Grill Feature:	Yes	Hot Plate (W):	Oven 1200W - Hotplates 1000W & 600W
Accessories:	2x oven shelf positions, 1x baking tray, 1x wire rack and 1x tray handle		

Cert Available: EMC/LVD    RoHs

## DIMENSIONS

Product information:	Individual Product	Packaging information:	Individual Packaging
Product Spec:		Packaging Spec:	
Width (mm):	488	Dimensions of export carton (LxDxH in mm):	N/A
Depth (mm):	322.5	Nb gift box / export carton:	N/A
Height (mm):	349	Gross Weight (kg):	7.87kgs
Volume (cbm):	N/A	Weight:	6.95kgs

