



VTX-900 Inrush Current Limiting Module:

Input Voltage: 230V 50/60Hz, +/-10%
 Output Voltage: 230V 50/60Hz, (Same as Input Voltage)
 Current Load: 25Amps Max
 Inrush Current < 90A
 Total Start Up Time: <2000mS
 Green LED 2: Working Normal
 Red LED 1: Fault Condition
 Fail Safe Relay default status: Open circuit.
 Fuse: Slow Blow 1Amp/250V
 Operational Temperature: -25 to +70°C

Schematic



Not to Scale
 Dimensions in Millimeters



VIGORTRONIX
 16 De Havilland Way
 Windrush Park, Witney
 Oxon, OX29 0YG, UK
 Tel: +44 (0)1993 777570
 Fax: +44 (0)1993 777580
 www.vigortronix.com

DRAWING
VTX-900 Drawing

Issue	Date	Drawn	PCN No	Checked
1	01-11-18	GPH		
2				
3				

DRAWING NUMBER
VTX-900
Inrush Limiter