

Mica Nozzle Heaters

High quality mica nozzle heaters for temperatures up to 300°C,
1 metre of cable



- Best quality Mica for high dielectric strength and maximum heat transfer
- Full width low expansion straps
- Specially treated finish to resist oxidation and enhance thermal conductivity
- High performance precision wound element for superior heat distribution
- 1 metre long stainless steel braided cable
- Recommended for temperatures up to 300°C
- 240V
- Wide range of applications including plastic process machinery, injection / blow moulding, rubber moulding, test equipment, food process industry etc.

Diameter	Length	Max.Temp	Power rating	Manufacturer's Part Number	Rapid Part Number
1"inch	1"inch	300°C	120W	XE-9500-001	61-3217
1"inch	1.5"inch	300°C	150W	XE-9501-001	61-3218
1.5"inch	1"inch	300°C	150W	XE-9503-001	61-3219
1.5"inch	1.5"inch	300°C	250W	XE-9504-001	61-3220
35mm	30mm	300°C	150W	XE-9502-001	61-3221
40mm	25mm	300°C	250W	XE-9505-001	61-3222
42mm	32mm	300°C	300W	XE-9506-001	61-3223
50mm	25mm	300°C	200W	XE-9507-001	61-3224
60mm	25mm	300°C	225W	XE-9508-001	61-3225