





Thermocouple Cable – PTFE Insulated Twin Twisted Pair



- PTFE twin twisted pair for extending or making simple thermocouples
- Single pair of PTFE insulated conductors twisted together
- Thermocouple type K with 1/0.2mm conductors
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Suitable for steam & pressure applications, autoclaves, sterilizers etc.
- 25, 50 & 100 metre reel lengths
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to IEC-584-3

<u>Calibration Type</u>	<u>Colour</u>	<u>No. of Strands</u>	<u>Product Code</u>	<u>Manufacturer's Part Number</u>	<u>Rapids Part Number</u>
K		1/0.2	25M - K 1/0.2 PTFE TTP IEC	XE-2142-025	61-3226
K		1/0.2	50M - K 1/0.2 PTFE TTP IEC	XE-2142-050	61-3227
K		1/0.2	100M - K 1/0.2 PTFE TTP IEC	XE-2142-100	61-3228