

## ENN05010

Mureva BOX - junction box - 10 grommets Ø25 +  
2xØ32 - 175x150x80 mm



### Main

Range of product	Mureva BOX
Product or component type	Junction box
Colour tint	Grey RAL 7035
Quantity per set	1 piece

### Complementary

Wiring device mounting	Surface
Cable entry	Grommets
Fixing mode	Screw-fixed cover
Base dimension	175 x 150 x 80 mm
Cable entry number	10 grommets Ø 25 mm 2 grommets Ø 32 mm
Material	PP (polypropylene) cover SBS (styrene butadiene styrene) grommet
Electrical insulation class	Class II according to IEC 536
Height	90 mm
Width	195 mm
Depth	165 mm
Product weight	0.4 kg

### Environment

ambient air temperature for operation	-25...40 °C
IP degree of protection	IP55 according to IEC 60529
IK degree of protection	IK07 according to EN 50102
fire resistance	750 °C
standards	EN 60670
product certifications	CE
environmental characteristic	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1026 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.