


Data Sheet

Jumper Wire Kit



Drawing:



Technical data

Wire: UL 1061 AWG22 with 14 kinds of lengths

Copper wire: Ø0.65 mm

PVC jacket: Ø1.15 mm

For wire (1)~(13) The length of bending feet: 7.2 ± 0.2 mm

For wire (1)~(13) The length of bending angle: 90°

For wire (14) The length of bending feet: 6.2 ± 0.2 mm

For wire (14) The length of bending angle: 90°

Bending feet without PVC: Nickel plated over copper

The parallel error of bending feet: $< 2^\circ$

Box size: 165 x 54 x 15 mm

140 pcs Jumper wires (14 lengths x 10 pcs each)