

NETGEAR M4300-24X24F/US/EMEA Managed 10G Ethernet (100/1000/10000) 1U Grey



Brand : NETGEAR

Product code: XSM4348S-100NES

Product name : M4300-24X24F/US/EMEA

NETGEAR Managed Switch with 24x10GBASE-T and 24xSFP+ for US and EMEA (Europe, Middle East and Africa) Regions

NETGEAR M4300-24X24F/US/EMEA Managed 10G Ethernet (100/1000/10000) 1U Grey:

NETGEAR Managed Switch with 24x10GBASE-T and 24xSFP+

NETGEAR M4300-24X24F is a NETGEAR 48-port managed switch used as a backbone switch for multi-tier AVoIP deployments. It features 24 10GBASE-T (copper RJ-45) ports, 24 10GBASE-X (fiber SFP+) ports and includes a 250W power supply unit.

NETGEAR M4300-24X24F/US/EMEA. Switch type: Managed. Basic switching RJ-45 Ethernet ports type: 10G Ethernet (100/1000/10000), Basic switching RJ-45 Ethernet ports quantity: 24, USB 2.0 ports quantity: 1, Console port: RJ-45. Switching capacity: 480 Gbit/s. Rack mounting, Form factor: 1U

Management features		Design	
Switch type *	Managed	Rack mounting *	✓
Ports & interfaces		Form factor	1U
Basic switching RJ-45 Ethernet ports quantity *	24	Product colour	Grey
Basic switching RJ-45 Ethernet ports type *	10G Ethernet (100/1000/10000)	Power	
10G Ethernet (copper) ports quantity	24	Power source *	AC
SFP+ module slots quantity	2	Power supply included *	✓
Console port	RJ-45	Power consumption (typical)	250 W
USB 2.0 ports quantity	1	Operational conditions	
Network		Heat dissipation	473.9 BTU/h
10G support *	✓	Weight & dimensions	
Optical fiber		Width	212 mm
Fiber ethernet cabling technology	10GBASE-T, 10GBASE-X	Depth	345 mm
Data transmission		Height	44 mm
Switching capacity *	480 Gbit/s	Weight	4.1 kg
Throughput	357 Mpps	Packaging data	
Latency (10 Gbps)	1.827 µs	Package width	570 mm
		Package depth	349 mm
		Package height	90 mm
		Package weight	5.7 kg



0606449110067



606449110067

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.