



Canon PGI-570PGBK Pigment Black Ink Cartridge

Brand : Canon

Product code: 0372C001

Product name : PGI-570PGBK Pigment Black Ink Cartridge

- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges+++
- Genuine Canon Ink provides consistent quality prints 100% of the time+++
- Genuine Canon Ink is 100% reliable so you can print with less stress+++
- Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
PGI-570PGBK Pigment Black Ink Cartridge

Canon PGI-570PGBK Pigment Black Ink Cartridge:

This pigment black ink is used for printing documents on plain paper and ensures crisp, sharp text with great longevity. The 15ml ink tank allows you to print up to 300* pages of A4 colour documents.
Canon PGI-570PGBK Pigment Black Ink Cartridge. Black ink type: Pigment-based ink, Black ink volume: 15 ml, Printing colours: Black, Quantity per pack: 1 pc(s), Black ink page yield: 300 pages

Features		Features	
Black ink type	Pigment-based ink	Type *	Original
Print technology	Inkjet printing	Ink type	Pigment-based ink
Compatibility *	PIXMA MG7750, PIXMA MG7751,	Printing colours *	Black
	PIXMA MG7752, PIXMA MG7753,	Brand compatibility *	Canon
	PIXMA MG6850, PIXMA MG6851,	Country of origin	Japan
		Packaging data	
Quantity per pack *	1 pc(s)	Package width	68 mm
Black ink cartridges quantity	1	Package depth	154 mm
Black ink volume	15 ml	Package height	30 mm
Black ink page yield *	300 pages	Package weight	60 g
		Logistics data	
		Harmonized System (HS) code	84439990





4549292032918

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.