

Targus CitySmart 12, 12.5, 13, 13.3, 14" SlimlineTopload Laptop Case

Brand : Targus

Product code: TBT913EU

Product name : CitySmart 12, 12.5, 13, 13.3, 14" SlimlineTopload Laptop Case

Slimline Topload Laptop Case - Black/Grey

Targus CitySmart 12, 12.5, 13, 13.3, 14" SlimlineTopload Laptop Case:

Description

Blending on the go functionality with urban styling the City Smart range is full of minimalist cool. Featuring an innovative Multi-Fit cradle in the padded laptop compartment, which can securely accommodate a range of different sized hardware, this laptop briefcase is designed to carry and protect laptops between 12 and 14" with a reassuringly snug fit. Combining a slim design with dedicated pockets and compartments for your accessories, this briefcase is ideal for the urban commuter. Padded adjustable shoulder strap ensures comfort while carrying.

Targus CitySmart 12, 12.5, 13, 13.3, 14" SlimlineTopload Laptop Case. Case type: Briefcase, Maximum screen size: 35.6 cm (14"), Number of front pockets: 1, Carrying handle(s), Shoulder strap. Weight: 610 g. Surface coloration: Monochromatic



Features		Weight & dimensions	
Surface coloration	Monochromatic	Notebook compartment dimensions (W x D x H)	349 x 25 x 249 mm
Maximum screen size *	35.6 cm (14")	Package width	390 mm
Case type *	Briefcase	Package depth	90 mm
Material *	Polyurethane	Package height	300 mm
Product main colour *	Black, Grey	Package weight	670 g
Expandable	✗	Logistics data	
Front pocket	✓	Products per pallet	110 pc(s)
Number of front pockets	1	Harmonized System (HS) code	84733080
Carrying handle(s)	✓	Master (outer) case width	410 mm
Shoulder strap	✓	Master (outer) case length	440 mm
Removable shoulder strap	✓	Master (outer) case height	340 mm
Country of origin	China	Master (outer) case gross weight	4.38 kg
Quantity	1	Products per master (outer) case	5 pc(s)
Weight & dimensions		Other features	
Width	64 mm	Minimum screen size	30.5 cm (12")
Depth	370 mm		
Height	360 mm		
Weight	610 g		

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date