

Ricoh fi-7480 ADF scanner 600 x 600 DPI A3 Grey, White

Brand : Ricoh

Product code: PA03710-B001

Product name : fi-7480

ADF, 600 x 600 dpi, 2 x CCD, 24 bit, 80 ppm, 160 ipm (200 & 300 DPI), USB 3.0, 7.6 kg
Ricoh fi-7480. Maximum scan size: 304.8 x 5588 mm, Optical scanning resolution: 600 x 600 DPI, Output colour depth: 24 bit. Scanner type: ADF scanner, Product colour: Grey, White. Sensor type: Dual CCD, Light source: White LED (4x), Scan drivers: ISIS, TWAIN. Auto document feeder (ADF) input capacity: 100 sheets. Maximum ISO A-series paper size: A3, Scanning media types supported: Plastic Card, ISO A-series sizes (A0...A9): A3, A4, A8



Scanning		Power	
Maximum scan size *	304.8 x 5588 mm	Power consumption (PowerSave)	1.4 W
Optical scanning resolution *	600 x 600 DPI	Input voltage	100-240 V
Colour scanning	✓	Weight & dimensions	
Duplex scanning *	✓	Width	380 mm
Output colour depth	24 bit	Depth	209 mm
Output greyscale depth	8 bit	Height	168 mm
Output monochrome depth	1 bit	Weight	7.6 kg
Film scanning	✗	Packaging data	
ADF scan speed (b/w, A4)	80 ppm	Quantity per pack	1 pc(s)
ADF scan speed (colour, A4)	80 ppm	Package width	505 mm
Duplex ADF scan speed (b/w, A4)	160 ipm	Package depth	302 mm
Duplex ADF scan speed (colour, A4)	160 ipm	Package height	330 mm
Black/white scanning colour modes	Grayscale, Monochrome	Package weight	9.9 kg
Design		Packaging content	
Scanner type *	ADF scanner	Cables included	AC
Product colour *	Grey, White	Quick start guide	✓
Built-in display *	✓	AC adapter included	✓
Performance		Drivers included	✓
Sensor type *	Dual CCD	Bundled software	PaperStream IP, PaperStream Capture, Software Operation Panel, Error Recovery Guide, Scanner Central Admin tools, ScanSnap Manager, Scan to Microsoft SharePoint, ABBYY FineReader, 2D barcode for PaperStream
Light source	White LED (4x)		
Scan drivers	ISIS, TWAIN		
Input capacity		Sustainability	
Auto document feeder (ADF) input capacity	100 sheets	Sustainability certificates	ENERGY STAR
Paper handling			
Scanning media types supported	Plastic Card		
Multi feed detection	✓		
Maximum ISO A-series paper size *	A3		

Paper handling		System requirements		
ISO A-series sizes (A0...A9)	A3, A4, A8		Windows 10 Enterprise, Windows 10 Enterprise x64, Windows 10 Home, Windows 10 Home x64, Windows 10 Pro, Windows 10 Pro x64, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows XP Professional x64	
Media thickness (min)	1.4 mm			
Plastic card media weight	27 - 413 g/m²			
Auto Document Feeder (ADF) media weight	27 - 413 g/m²			
Maximum scan width	30.5 cm			
Maximum scan length	5.588 mm			
Maximum scan area (ADF)	304.8 x 431.8 mm			
Minimum scan area (ADF)	50.8 x 69 mm			
Ports & interfaces		Windows operating systems supported		
USB port *	✓			
USB version	3.2 Gen 1 (3.1 Gen 1)			
USB connector type	USB Type-B			
Socket connector type	C5			
Standard interfaces	USB 3.2 Gen 1 (3.1 Gen 1)	Server operating systems supported	Windows Server 2008, Windows Server 2008 R2 x64, Windows Server 2008 x64, Windows Server 2012 R2 x64, Windows Server 2012 x64, Windows Server 2016 x64	
Power				
Power supply type *	AC			
Power consumption (typical)	43 W			
Power consumption (standby)	0.35 W			
Power consumption (off)	0.35 W			
Operational conditions				
Operating temperature (T-T)		5 - 35 °C		
Operating relative humidity (H-H)		20 - 80%		
Other features				
Compliance certificates		RoHS		
Selectable background colour		✓		
Background colours		Black, White		
Logistics data				
Country of origin		Indonesia		
Pallet gross length		121.9 cm		
Pallet gross width		101.6 cm		
Harmonized System (HS) code		8471607000		
Paper packaging weight		2.4 kg		
Metal packaging weight		0 g		
Wood packaging weight		0 g		
Plastic packaging weight		15 g		
Products per pallet (air)		24 pc(s)		
Products per pallet (sea)		40 pc(s)		
Pallet height (sea)		180 cm		
Pallet height (air)		114 cm		
Cardboard packaging weight		1.2 kg		
Foil packaging weight		15 g		
Polystyrene (EPS/EPP) packaging weight		200 g		
Glass packaging weight		0 g		



4939761308444

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.