

NETGEAR APM402XL-10000S network switch module 40 Gigabit Ethernet


Brand : NETGEAR Product code: APM402XL-10000S
Product name : APM402XL-10000S

40G Fiber card, 2 x QSFP+

NETGEAR APM402XL-10000S network switch module 40 Gigabit Ethernet:

The M4300 Stackable L3 Managed Switch Series comes with 40G, 10G and 1G models in a variety of form factors including PoE+ full provisioning. SDN-ready with OpenFlow 1.3, M4300 Switch Series delivers IPv4/IPv6 rich services for mid-enterprise edge and SMB core with mixed stacking between 40-, 10- and 1-Gigabit models. Layer 3 feature set includes static and policy-based routing, RIP, VRRP, OSPF, and PIM dynamic routing. M4300 is ideal for server aggregation, wireless access, unified communications and Video-over-IP. NETGEAR APM402XL-10000S. Ethernet interface type: 40 Gigabit Ethernet, Ethernet LAN data rates: 40000 Mbit/s. Fiber optic connector: QSFP+. Bandwidth: 40 Gbit/s. Compatibility: Netgear M4300. Weight: 300 g

Network		Ports & interfaces	
Ethernet interface type	40 Gigabit Ethernet	Installed QSFP+ modules quantity	2
Ethernet LAN data rates	40000 Mbit/s	Performance	
Optical fiber		Compatibility	Netgear M4300
Fiber optic connector	QSFP+	Weight & dimensions	
Data transmission		Weight	300 g
Bandwidth	40 Gbit/s	Logistics data	
Ports & interfaces		Harmonized System (HS) code	85176990
Fiber ports quantity	2		



0606449133868



606449133868

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.