

Brother LC1220BKBP2 ink cartridge 2 pc(s) Original Black

Brand : Brother

Product code: LC1220BKBP2

Product name : LC1220BKBP2

- Each cartridge prints 300 pages in accordance with ISO/IEC 24711
- High quality genuine Brother cartridges
- Prevents waste to save you paper, time and money

The Brother LC1220BKBP2 Black Ink Cartridge – Twin Pack. Each cartridge prints 300 pages.

Brother LC1220BKBP2 ink cartridge 2 pc(s) Original Black:

Time to refill the black ink in your Brother printer? Then you need this genuine Brother LC1220BKBP2 Ink Cartridge Twin Pack. It means you can replace your black ink cartridge now, plus have a spare to hand the next time you need one.

Brother LC1220BKBP2. Black ink type: Pigment-based ink, Supply type: Twin pack, Printing colours: Black, Quantity per pack: 2 pc(s), Black ink page yield: 300 pages



Features		Weight & dimensions	
Black ink type	Pigment-based ink	Depth	121 mm
Compatibility *	DCPJ925DW DCP-J525W	Height	177 mm
	MFCJ625DW MFCJ825DW MFCJ430W	Weight	106 g
	DCPJ725DW	Packaging data	
Quantity per pack *	2 pc(s)	Package weight	162 g
Black ink cartridges quantity	2	Logistics data	
Black ink page yield *	300 pages	Pallet gross height	16.3 cm
Type *	Original	Products per pallet	1216 pc(s)
Ink type	Pigment-based ink	Master (outer) cases per pallet	304 pc(s)
Printing colours *	Black	Layers per pallet	8 pc(s)
Brand compatibility *	Brother	Master (outer) cases per pallet layer	38 pc(s)
Supply type *	Twin pack	Pallet gross weight	192.8 kg
Country of origin	Malaysia	Harmonized System (HS) code	84439990
Weight & dimensions		Pallet type	1200 x 1000 mm
Width	58 mm		



5014047562877

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.