



**APC Rack PDU, 2G, metered by outlet, with switching, 0U, 30A, 200V and 208V, 21 C13 and 3 C19 sockets**

**Brand :** APC

**Product code:** AP8641


**Product name :** APC Rack PDU, 2G, metered by outlet, with switching, 0U, 30A, 200V and 208V, 21 C13 and 3 C19 sockets

APC Rack PDU, 2G, metered by outlet, with switching, 0U, 30A, 200V and 208V, 21 C13 and 3 C19 sockets

APC Rack PDU, 2G, metered by outlet, with switching, 0U, 30A, 200V and 208V, 21 C13 and 3 C19 sockets. PDU types: Switched, Rack capacity: 0U, Product colour: Black. AC outlets quantity: 24 AC outlet(s), Power plug: NEMA L6-30P. Cable length: 3 m. Nominal input voltage: 200-230 V, Maximum current: 30 A, AC input frequency: 50 - 60 Hz. Compliance certificates: RoHS, Certification: cUL,FCC 15 A,ICES-003,UL,VCCI A

| Design                               |                                 | Operational conditions              |             |
|--------------------------------------|---------------------------------|-------------------------------------|-------------|
| PDU types *                          | Switched                        | Operating temperature (T-T)         | -5 - 45 °C  |
| Rack capacity *                      | 0U                              | Storage temperature (T-T)           | -25 - 65 °C |
| Product colour                       | Black                           | Operating relative humidity (H-H)   | 5 - 95%     |
| Ports & interfaces                   |                                 | Storage relative humidity (H-H)     | 5 - 95%     |
| AC outlets quantity *                | 24 AC outlet(s)                 | Operating altitude                  | 0 - 3000 m  |
| Power plug                           | NEMA L6-30P                     | Non-operating altitude              | 0 - 15000 m |
| Features                             |                                 | Weight & dimensions                 |             |
| Cable length                         | 3 m                             | Width                               | 56 mm       |
| Power                                |                                 | Depth                               | 51 mm       |
| Nominal input voltage *              | 200-230 V                       | Height                              | 1829 mm     |
| AC input frequency                   | 50 - 60 Hz                      | Weight                              | 8.23 kg     |
| Maximum current *                    | 30 A                            | Packaging data                      |             |
| Nominal output voltage               | 208 V                           | Package weight                      | 10.5 kg     |
| Maximum total current draw per phase | 30 A                            | Package width                       | 162 mm      |
| Power protection features            | Overload                        | Package depth                       | 118 mm      |
| Certificates                         |                                 | Package height                      | 2038 mm     |
| Compliance certificates              | RoHS                            | Logistics data                      |             |
| Certification                        | cUL,FCC 15 A,ICES-003,UL,VCCI A | Total carbon footprint (kg of CO2e) | 8153.67     |





0731304276975



731304276975

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.