



Everyday™ Mono Remanufactured Toner by Xerox compatible with Brother TN2220, High capacity

Brand : Xerox

Product family: Everyday
Remanufactured

Product code: 106R02634

Product name : Everyday™
Mono Remanufactured Toner by
Xerox compatible with Brother
TN2220, High capacity




Everyday™ Mono Remanufactured Toner by Xerox compatible with Brother TN2220, High capacity

Everyday™ Mono Remanufactured Toner by Xerox compatible with Brother TN2220, High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Mono Remanufactured Toner by compatible with Brother TN2220, High capacity. Black toner page yield: 2600 pages, Printing colours: Black, Quantity per pack: 1 pc(s)



Features		Operational conditions	
Compatibility *	DCP-7060D DCP-7065DN FAX-2840 FAX-2940 HL-2220 HL-2230 HL-2240/HL-2240D HL-2250DN HL-2270DW HL-2275DW HL-2280DW MFC-7240 MFC-7360N/7460DN/7860DW	Storage relative humidity (H-H)	35 - 85%
		Weight & dimensions	
Quantity per pack *	1 pc(s)	Weight	635 g
Black toner page yield *	2600 pages	Packaging data	
Type *	Compatible	Package width	160 mm
Printing colours *	Black	Package depth	365 mm
Brand compatibility *	Brother	Package height	115 mm
Supply type *	Single pack	Package weight	980 g
Cartridge capacity	High (XL) Yield	Package type	Box
OEM code	TN2220	Other features	
Country of origin	Vietnam	Colour	×
		Page yield footnote	ISO/IEC 19798
		Certification	RoHS, REACH SVHC, CE MARK STMC, ISO 9001:2015, ISO 14001:2015
Operational conditions		Logistics data	
Operating temperature (T-T)	17 - 25 °C	Harmonized System (HS) code	8443.99.1000
Operating relative humidity (H-H)	30 - 70%	Products per master (outer) case	10 pc(s)
Storage temperature (T-T)	0 - 35 °C		



0952059663050



952059663050



0095205966305



95205966305

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.