

StarTech.com Cat6 Patch Cable - Shielded (SFTP) - 0.5 m, Blue

Brand : StarTech.com

Product code: N6SPAT50CMBL

Product name : Cat6 Patch Cable - Shielded (SFTP) - 0.5 m, Blue

StarTech.com Cat6 Patch Cable - Shielded (SFTP) - 0.5 m, Blue
StarTech.com Cat6 Patch Cable - Shielded (SFTP) - 0.5 m, Blue. Cable length: 0.5 m, Cable standard: Cat6, Cable shielding: S/FTP (S-STP), Connector 1: RJ-45, Connector 2: RJ-45, Data transfer rate: 1000 Mbit/s, Product colour: Blue



Features		Features	
Product colour *	Blue	Plug and Play	✓
Cable length *	0.5 m	Certificates	
Cable standard *	Cat6	Compliance certificates	RoHS
Cable shielding *	S/FTP (S-STP)	Certification	TIA/EIA-568-B.1-2001 T568B
Connector 1 *	RJ-45	Weight & dimensions	
Connector 2 *	RJ-45	Weight	28 g
Connector 1 gender *	Male	Packaging content	
Connector 2 gender *	Male	Quantity per pack	1 pc(s)
Jacket material	Polyvinyl chloride (PVC)	Packaging data	
Cable rating	CMG (CM)	Package width	200 mm
Cabling technology	10/100/1000Base-T(X)	Package depth	220 mm
AWG wire size	26	Package height	10 mm
Data transfer rate	1000 Mbit/s	Package weight	38 g
Frequency	500 MHz	Logistics data	
Snagless cable boot	✓	Harmonized System (HS) code	84733080



0065030863339



065030863339

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.