



## 3M PF195W9B display privacy filter 49.5 cm (19.5") Monitor

### Frameless display privacy filter

**Brand :** 3M

**Product code:** PF195W9B

**Product name :** PF195W9B

- Effective "black out" privacy from side views outside the 60-degree viewing angle
  - Reversible between a glossy side and glare-reducing matte
  - Matte surface helps reduce glare and fingerprints
  - Helps reduce blue light, without distorting the natural color of your display
  - Adds an extra layer of protection from everyday scratches and dust
  - Easy to attach, remove and clean
  - Durable privacy filter that can withstand hundreds of cleanings
  - Compatible with most touchscreen displays
  - 100% hand inspected for quality assurance
- 3M™ Privacy Filter for 19.5in Monitor, 16:9, PF195W9B


#### 3M PF195W9B display privacy filter 49.5 cm (19.5") Monitor Frameless display privacy filter:

3M™ Privacy Filters provide world-class "black out" privacy from side views outside the 60-degree viewing angle, while creating an excellent viewing experience from straight on views. Reversible between a glossy side and a glare-reducing matte side that helps reduce reflections and hide fingerprints, so you can enjoy pristine image clarity.

| Design                        |                                  | Packaging data                       |                 |
|-------------------------------|----------------------------------|--------------------------------------|-----------------|
| Maximum screen size *         | 49.5 cm (19.5")                  | Package width                        | 469.9 mm        |
| Suitable for *                | Monitor                          | Package depth                        | 2.54 mm         |
| Type *                        | Frameless display privacy filter | Package height                       | 342.9 mm        |
| Filter colour                 | Black                            | Package weight                       | 218.450085392 g |
| Product colour                | Black                            | Logistics data                       |                 |
| Features                      |                                  | Pallet net height                    | 121.9 cm        |
| Display filter features *     | Anti-glare, Privacy              | Pallet net length                    | 121.9 cm        |
| Aspect ratio                  | 16:9                             | Pallet net width                     | 106.7 cm        |
| Widescreen                    | ✓                                | Pallet net weight                    | 53.1 kg         |
| Scratch-resistant             | ✓                                | Pallet weight (EU)                   | 264.4 kg        |
| Protection features           | Scratch-resistant                | Products per pallet (EU)             | 805 pc(s)       |
| Easy to clean                 | ✓                                | Harmonized System (HS) code          | 85299097        |
| Durable screen protection     | ✓                                | Shipping (inner) case width          | 35.2 cm         |
| Privacy filtering orientation | Landscape                        | Shipping (inner) case length         | 48.1 cm         |
| Touchscreen compatible        | ✓                                | Shipping (inner) case height         | 4.76 cm         |
| Easy to remove                | ✓                                | Shipping (inner) case gross weight   | 1.5 kg          |
| Blue light filter             | ✓                                | Shipping (inner) case net weight     | 329.988449175 g |
| Weight & dimensions           |                                  | Products per shipping (inner) case   | 5 pc(s)         |
| Width                         | 433 mm                           | Shipping (inner) case GTIN (EAN/UPC) | 51128830826     |
| Height                        | 237 mm                           |                                      |                 |
| Weight                        | 65.997689835 g                   |                                      |                 |



(01)50051128830821



0051128830826



051128830826

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.