



Lenovo 10G SW iSCSI SFP+ network transceiver module 10000 Mbit/s SFP+

Brand : Lenovo

Product code: 00WC087

Product name : 10G SW iSCSI SFP+




Lenovo Storage S2200/S3200 10Gb SW Optical iSCSI SFP+ Module 1 pack

Lenovo 10G SW iSCSI SFP+ network transceiver module 10000 Mbit/s SFP+:

SFP Transceivers are compliant with the Multi-Source Agreement (MSA) ensuring compatibility with a wide range of networking equipment. Select your choice of Copper or Fiber versions that support Fast Ethernet and 10/Gigabit Ethernet speeds.
Lenovo 10G SW iSCSI SFP+. Maximum data transfer rate: 10000 Mbit/s, Interface type: SFP+, SFP transceiver standard: SW. Compatible products: Lenovo Storage S2200/S3200. Certification: MSA. Width: 13.4 mm, Depth: 56.5 mm, Height: 8.5 mm. Quantity per pack: 1 pc(s)

Performance		Operational conditions	
Maximum data transfer rate *	10000 Mbit/s	Operating temperature (T-T)	0 - 70 °C
Interface type *	SFP+	Storage temperature (T-T)	-40 - 85 °C
SFP transceiver standard	SW	Operating relative humidity (H-H)	10 - 80%
Networking standards	IEEE 802.3, IEEE 802.3ab, IEEE 802.3ae, IEEE 802.3u	Storage relative humidity (H-H)	10 - 85%
Auto MDI/MDI-X	✓	Weight & dimensions	
Features		Width	13.4 mm
Hot-Plug support	✓	Depth	56.5 mm
Compatible products	Lenovo Storage S2200/S3200	Height	8.5 mm
Certificates		Packaging content	
Certification	MSA	Quantity per pack	1 pc(s)



0889488055883



889488055883

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.