

Epson Turtle T1573 Vivid Magenta

Brand : Epson

Product family: Turtle

Product code: C13T15734010

Product name : T1573 Vivid Magenta

- Excellent colour stability
 - Exceptional light-fastness
 - Excellent black and white image quality with three levels of black
- T1573 Vivid Magenta

Epson Turtle T1573 Vivid Magenta:

Epson UltraChrome K3 inks are well known for their wide gamut and accurate colour rendition with virtually no colour twist. Now, with the addition of newly formulated vivid magenta and vivid light magenta inks, they offer an even wider colour gamut with a dramatically improved range of expression. Epson Turtle T1573 Vivid Magenta. Colour ink type: Pigment-based ink, Cartridge capacity: High (XL) Yield, Colour ink page yield: 2300 pages, Colour ink volume: 25.9 ml, Printing colours: Vivid magenta, Quantity per pack: 1 pc(s)

Features		Packaging data	
Colour ink type	Pigment-based ink	Package depth	33 mm
Print technology	Inkjet printing	Package height	120 mm
Compatibility *	- Epson Stylus Photo R3000	Package type	Blister
Quantity per pack *	1 pc(s)	Logistics data	
Colour ink cartridges quantity	1	Pallet gross width	80 cm
Colour ink volume	25.9 ml	Pallet gross length	120 cm
Colour ink page yield *	2300 pages	Pallet gross height	48 cm
Type *	Original	Products per pallet	2400 pc(s)
Cartridge capacity	High (XL) Yield	Harmonized System (HS) code	84439990
Ink type	Pigment-based ink	Pallet width (UK)	100 cm
Printing colours *	Vivid magenta	Pallet length (UK)	120 cm
OEM code	C13T15734010	Pallet height (UK)	48 cm
Country of origin	China	Products per pallet (UK)	2400 pc(s)
Colour	✔	Products per pallet layer	240 pc(s)
Packaging data		Products per pallet layer (UK)	240 pc(s)
Package width	145 mm	Minimum order quantity	8 pc(s)




3610170032496




5053973952550



8715946479453



8715946487977



4053162273726



4053617031840



5053676863368




5054484337140



5054629238622



5054533337145



5053460786378

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.