

NETGEAR M4300-28G-PoE+(1000W)/US/EMEA Managed Gigabit Ethernet (10/100/1000) Power over Ethernet (PoE) 1U Black



Brand : NETGEAR

Product code: GSM4328PB-100NES

Product name : M4300-28G-PoE+(1000W)/US/EMEA

Managed Switch with 24x1G PoE+ and 4x10G for US and EMEA (Europe, Middle East and Africa) Regions

NETGEAR M4300-28G-PoE+(1000W)/US/EMEA Managed Gigabit Ethernet (10/100/1000) Power over Ethernet (PoE) 1U Black:

M4300–28G–PoE+ (1000W PSU) is a NETGEAR managed switch for KDS–8 copper deployments. It features 24 24 1G PoE+ ports and 4 independent 10G ports (2 10GBASE–T ports and 2 SFP+ Layer 3 ports). It also includes a 1000W power supply unit.
NETGEAR M4300-28G-PoE+(1000W)/US/EMEA. Switch type: Managed. Basic switching RJ-45 Ethernet ports type: Gigabit Ethernet (10/100/1000), Basic switching RJ-45 Ethernet ports quantity: 24, Installed SFP+ modules quantity: 2, USB 2.0 ports quantity: 1, Console port: RJ-45. Switching capacity: 128 Gbit/s. Power over Ethernet (PoE). Form factor: 1U

Management features		Data transmission	
Switch type *	Managed	Switching capacity *	128 Gbit/s
Quality of Service (QoS) support	✗	Latency (10 Gbps)	2.72 μs
Ports & interfaces		Design	
Basic switching RJ-45 Ethernet ports quantity *	24	Stackable *	✓
Basic switching RJ-45 Ethernet ports type *	Gigabit Ethernet (10/100/1000)	Form factor	1U
Installed SFP+ modules quantity *	2	Product colour	Black
SFP+ module slots quantity	2	Number of fans	1 fan(s)
Console port	RJ-45	Performance	
USB 2.0 ports quantity	1	Noise level	39.8 dB
Network		Mean time between failures (MTBF)	1189685 h
10G support *	✓	Power	
Copper ethernet cabling technology	1000BASE-T	Power supply included *	✓
Optical fiber		Power over Ethernet (PoE)	
Fiber ethernet cabling technology	10GBASE-T, 10GBASE-X	Power over Ethernet (PoE) *	✓
Operational conditions			
		Heat dissipation	1969.88 BTU/h
Weight & dimensions			
		Width	482.6 mm



0606449112801



606449112801

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.