



Lenovo 7m QSFP+ InfiniBand/fibre optic cable QSFP+

Brand : Lenovo

Product code: 00D5813

Product name : 7m QSFP+

7m Passive QSFP+ to QSFP+ Cable

Lenovo 7m QSFP+ InfiniBand/fibre optic cable QSFP+:

QSFP+ provides flexible connectivity for 40Gb Ethernet. For 40Gb-to-40Gb connectivity, clients can use QSFP+ Direct Attach Cables up to 7 meters. For 40Gb connectivity over longer distances, use a QSFP+ transceiver and QSFP+ MTP optical cables. To increase the number of available 10Gb ports, use QSFP+ DAC Break Out Cables to split out each 40Gb port and connect up to four 10Gb SFP+ external ports using copper or leverage the eSR4 Transceiver and 40G eSR4 MTP-4xLC OM3 MMF Breakout Cables for distances up to 300 meters. For 40Gb connectivity over longer distances, use a QSFP+ transceiver and QSFP+ MTP optical cables.

Lenovo 7m QSFP+. Cable length: 7 m, Connector 1: QSFP+, Connector 2: QSFP+



Features		Features	
Cable length *	7 m	Connector 2 *	QSFP+
InfiniBand protocol	✓	Data transfer rate	40 Gbit/s
Connector 1 *	QSFP+	Logistics data	
		Harmonized System (HS) code	85444290



0883436240956



883436240956



4053162143333

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.