

Brother LC3211Y ink cartridge 1 pc(s) Original Standard Yield Yellow

Brand : Brother

Product code: LC3211Y

Product name : LC3211Y

- Prints 200 pages in accordance with ISO/IEC24711
 - High quality genuine Brother cartridge
 - Prevents waste to save you paper, time and money
- Genuine Brother LC3211Y standard yield yellow ink cartridge - single pack. Prints up to 200 pages.




Brother LC3211Y ink cartridge 1 pc(s) Original Standard Yield Yellow:

For the finest quality printouts every time, choose the Brother LC3211Y ink cartridge in yellow. Why risk print problems by buying a non-branded refill cartridge when this genuine Brother supply is guaranteed to keep your printer working at its best?

Brother LC3211Y. Colour ink type: Pigment-based ink, Cartridge capacity: Standard Yield, Supply type: Single pack, Colour ink page yield: 200 pages, Printing colours: Yellow, Quantity per pack: 1 pc(s)

Features		Weight & dimensions	
Colour ink type	Pigment-based ink	Weight	36 g
Print technology	Inkjet printing	Packaging data	
Compatibility *	DCP-J772DW DCP-J774DW MFC-J890DW MFC-J895DW DCP-J572DW MFC-J491DW MFC-J497DW	Package width	148 mm
Quantity per pack *	1 pc(s)	Package depth	95 mm
Colour ink cartridges quantity	1	Package height	18 mm
Colour ink page yield *	200 pages	Package weight	40 g
Type *	Original	Package type	Blister
Cartridge capacity	Standard Yield	Other features	
Ink type	Pigment-based ink	Certification	ISO/IEC24711
Printing colours *	Yellow	Logistics data	
Brand compatibility *	Brother	Pallet gross height	18 cm
Supply type *	Single pack	Products per pallet	6000 pc(s)
OEM code	LC-3211	Master (outer) cases per pallet	60 pc(s)
Country of origin	Philippines	Layers per pallet	6 pc(s)
Weight & dimensions		Master (outer) cases per pallet layer	10 pc(s)
Width	15 mm	Pallet gross weight	255.6 kg
Depth	85 mm	Harmonized System (HS) code	84439990
Height	120 mm	Pallet type	800 x 1200 mm



4977766775779



5715328103269

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.