

Brother LC3213C ink cartridge 1 pc(s) Original High (XL) Yield Cyan

Brand : Brother

Product code: LC3213C

Product name : LC3213C

- Prints 400 pages in accordance with ISO/IEC24711
 - High quality genuine Brother cartridge
 - Prevents waste to save you paper, time and money
- Genuine Brother LC3213C high yield cyan ink cartridge - single pack. Prints up to 400 pages.

Brother LC3213C ink cartridge 1 pc(s) Original High (XL) Yield Cyan:

For the finest quality printouts every time, choose the Brother LC3213C ink cartridge in cyan. Why risk print problems by buying a non-branded refill cartridge when this genuine Brother supply is guaranteed to keep your printer working at its best?

Brother LC3213C. Cartridge capacity: High (XL) Yield, Supply type: Single pack, Colour ink page yield: 400 pages, Printing colours: Cyan, Quantity per pack: 1 pc(s)



Features		Packaging data	
Print technology	Inkjet printing	Package width	9 mm
Compatibility *	DCP-J772DW DCP-J774DW MFC-	Package depth	100 mm
	J890DW MFC-J895DW DCP-J572DW	Package height	52 mm
	MFC-J491DW MFC-J497DW	Package weight	39 g
Quantity per pack *	1 pc(s)	Package type	Blister
Colour ink cartridges quantity	1	Other features	
Colour ink page yield *	400 pages	Certification	ISO/IEC24711
Type *	Original	Logistics data	
Cartridge capacity	High (XL) Yield	Pallet gross height	18 cm
Printing colours *	Cyan	Products per pallet	6000 pc(s)
Brand compatibility *	Brother	Master (outer) cases per pallet	60 pc(s)
Supply type *	Single pack	Layers per pallet	6 pc(s)
OEM code	LC-3213	Master (outer) cases per pallet layer	10 pc(s)
Country of origin	Philippines	Pallet gross weight	304.8 kg
Weight & dimensions		Harmonized System (HS) code	84439990
Width	15 mm	Pallet type	800 x 1200 mm
Depth	90 mm		
Height	115 mm		
Weight	36 g		



2509062115434



4977766762267



5715328103283

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.