



## Everyday™ Cyan Remanufactured Toner by Xerox compatible with HP 126A (CE311A), Standard capacity

**Brand :** Xerox

**Product family:** Everyday  
Remanufactured

**Product code:** 106R02258



**Product name :** Everyday™  
Cyan Remanufactured Toner by  
Xerox compatible with HP 126A  
(CE311A), Standard capacity


Everyday™ Cyan Remanufactured Toner by Xerox compatible with HP 126A (CE311A), Standard capacity

Everyday™ Cyan Remanufactured Toner by Xerox compatible with HP 126A (CE311A), Standard capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Cyan Remanufactured Toner by compatible with HP 126A (CE311A), Standard capacity.

Colour toner page yield: 1000 pages, Printing colours: Cyan, Quantity per pack: 1 pc(s)



| Features                          |                                                   | Operational conditions           |                                                            |
|-----------------------------------|---------------------------------------------------|----------------------------------|------------------------------------------------------------|
| Compatibility *                   | Color LaserJet 100 M175 MFP Color LaserJet CP1025 | Storage relative humidity (H-H)  | 35 - 85%                                                   |
| Quantity per pack *               | 1 pc(s)                                           | Weight & dimensions              |                                                            |
| Colour toner page yield *         | 1000 pages                                        | Weight                           | 305 g                                                      |
| Type *                            | Compatible                                        | Packaging data                   |                                                            |
| Printing colours *                | Cyan                                              | Package width                    | 110 mm                                                     |
| Brand compatibility *             | HP                                                | Package depth                    | 320 mm                                                     |
| Supply type *                     | Single pack                                       | Package height                   | 110 mm                                                     |
| Cartridge capacity                | Standard Yield                                    | Package weight                   | 530 g                                                      |
| Replacement for                   | HP 126A                                           | Package type                     | Box                                                        |
| OEM code                          | CE311A                                            | Other features                   |                                                            |
| Country of origin                 | Portugal                                          | Colour                           | ✓                                                          |
| Operational conditions            |                                                   | Certification                    | Nordic Swan/ISO14001/RoHs/Reach<br>STMC - ISO9001/ISO19752 |
| Operating temperature (T-T)       | 17 - 25 °C                                        | Logistics data                   |                                                            |
| Operating relative humidity (H-H) | 30 - 70%                                          | Harmonized System (HS) code      | 8443.99.1000                                               |
| Storage temperature (T-T)         | 0 - 35 °C                                         | Products per master (outer) case | 6 pc(s)                                                    |



0095205859904



095205859904

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date