



**APC NetShelter Cable Management, Horizontal Cable Manager,
2U, Single Side with Cover, Black, 482.6 x 88.9 x 165.1 mm**

Brand : APC

Product code: AR8606

Product name : APC NetShelter Cable Management,
Horizontal Cable Manager, 2U, Single Side with Cover, Black,
482.6 x 88.9 x 165.1 mm

APC NetShelter Cable Management, Horizontal Cable Manager, 2U, Single Side with Cover, Black, 482.6 x 88.9 x 165.1 mm

APC NetShelter Cable Management, Horizontal Cable Manager, 2U, Single Side with Cover, Black, 482.6 x 88.9 x 165.1 mm:

High density 2U, 6-in (150-mm) deep, horizontal cable manager AR8606 with cover. Features cable tie-off and cable access slots in the backplate for front to back cable pass-through.
APC NetShelter Cable Management, Horizontal Cable Manager, 2U, Single Side with Cover, Black, 482.6 x 88.9 x 165.1 mm. Type: Cable management panel, Product colour: Black. Weight: 1 kg

Features		Weight & dimensions	
Type *	Cable management panel	Height	89 mm
Product colour *	Black	Weight	1 kg
Built-in fan	✗	Packaging data	
Rack capacity	2U	Package width	521 mm
Hot-swap	✗	Package depth	200 mm
On/off switch	✗	Package height	153 mm
Castor wheels	✗	Package weight	1.25 kg
Locking	✗	Technical details	
Certification	TAA, REACH	Total carbon footprint (kg of CO2e)	3.79
Weight & dimensions		Compliance certificates	RoHS
Width	483 mm	Logistics data	
Depth (max)	16.6 cm	Harmonized System (HS) code	85389099



7313042915410




0731304291541



731304291541



5054484453086



5054629042434

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.